



Philips Prestigo
Universal remote control

PRESTiGO

SRT9320

Touch screen

See only the keys you need

A smart Universal Remote Control with a full-color touch screen that controls up to 20 devices out of 300.000 devices and only shows the keys you need.

Single control solution for most devices & brands

- Universal IR code database

Effortless set-up

- Easily learn and label extra functionality
- On-line updates via internet library
- Step by step guidance on the screen

Fast, easy access to your entertainment

- Activities to control multiple devices
- Direct access to your favorite channels

Intuitive Navigation

- 2.8" full - color screen
- Touch sensitive screen for easy navigation
- Most frequently used hard keys

PHILIPS
sense and simplicity

Specifications

Convenience

- Backlight
- **Universal IR database:** TV, VCR, DVD, SAT, CABLE, CD/MD, RECEIVER, AMP, PVR, Home Theater, PC, TAPE, DVR, DSS, DMR, DVB-T/S, DVDR, DVDR-HDD combo, DVD-VCR combo, Game, HTS, Projector (IR), Tuner, TV-DVD combo, TV-VCR combo, TV-VCR-DVD combo, VCD, Laser Disk, Audio system, Blue-Ray, HD-DVD player, HDR, Minidisc, MP3 Player Dock, Phone
- **On-Screen Display languages:** English, Dutch, German, French, Italian, Spanish, Russian, Portuguese
- Battery low indication
- **Display Type:** LCD
- **Channel icon library:** 500
- **Programmable channel icons:** 100
- **CD-ROM:** PrestigoSync software, Manual
- Copy key function
- **Languages in manual:** English, French, Spanish, Portuguese
- **Number of activities:** 20
- **Number of devices:** 300,000
- **Number of keys:** 22
- On line updates

Power

- **Battery saving manager:** Auto switch on/off
- Charger Cable
- Batteries included
- Rechargeable

Infrared Capabilities

- **Carrier frequency range:** 19kHz - 455kHz
- Learning IR codes
- **Operating distance:** 33 ft (10 m)
- **Transmission angle:** 90 degree
- Universal IR code database

System Specifications

- **Flash memory size:** 8 MB

Packaging dimensions

- **Packaging dimensions (W x H x D):** 15,8 x 30 x 7 cm
- **Nett weight:** 0,151 kg
- **Gross weight:** 0,373 kg
- **Tare weight:** 0,222 kg
- **EAN:** 87 12581 45973 4
- **Type of shelf placement:** Dummy
- **Number of products included:** 1
- **Packaging type:** Dummy

Outer Carton

- **Outer carton (L x W x H):** 30,3 x 16 x 14,3 cm
- **Nett weight:** 0,302 kg
- **Gross weight:** 0,966 kg
- **Tare weight:** 0,664 kg
- **GTIN:** 1 87 12581 45973 1
- **Number of consumer packagings:** 2

Accessories

- USB cable

Picture/Display

- Touch panel

Product highlights

Activity based control

Instead of operating your components one by one, activity based control blends the most commonly used functions into activities such as "Watch a movie" or "Listen to Music". For instance when a user selects 'watch a movie', than each individual piece of equipment - such as DVD player, TV and multimedia receiver -, will be switched on with one button press and all necessary commands will be executed, like selecting the right input, switch on the DVD player and start playing.

Direct favorite channel access

The remote control incorporates a library of channel icons for most countries' main TV and radio stations. Via the color LCD screen you can program the right channel icons for the right channel. Once setup, you use the LCD screen info to zap through your favorite channels using the icons of the stations instead of the digit keys on your remote.

Easily learn and label

Learning functionality refers to the process through which a remote control captures and stores infrared signals from other remotes for later use. When device codes are not included in the on-board database, they can always be learned from the original remote, simply by pointing to it. The improved way of adding and labeling functions makes it easier and faster to add extra functionality. So, no more missing functions.

Guided setup

Unlike other universal remote controls, where a 4-digit code needs to be entered to identify a brand and device, this remote incorporates on-device step-by-step instructions to setup your equipment, regardless of brand.

Internet library

Online updates are possible via a USB connection to your PC. The Philips PrestigoSync software (provided on a CD-rom or retrieved from the official Philips website) enables you to select your favorites from the latest database library, which contains over thousands of channel icons. With the Philips PrestigoSync software you will also be automatically informed of the latest available firmware for your Prestigo.

Universal IR code database

A universal IR code database refers to a library of infrared codes built-in to a particular remote. This feature allows a remote to control your equipment without needing to learn individual signals. The correct infrared code set is selected from the remote database via automatic search. This enables you to control of virtually every audio/video system element on the market today – regardless of model or brand.

2.8" full - color screen

A 2,8" (240 x 320 pixels) full-color LCD display which provides a high resolution quality, easy readability and navigation.

Intuitive touch screen

A touch sensitive screen which shows only the keys you need and allows you to navigate fast through the remote screen.



Issue date 2009-01-20

Version: 1.0.5

12 NC: 8670 000 48419
EAN: 87 12581 45973 4

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com